

# Clevis foot LN-40

Part number: 5148

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Product weight	192 g
Note on materials	RoHS-compliant
Mounting material	Tempered steel