

Coupling EAMD-56-54-18-23X27

Part number: 5225774

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Diameter of holder 1 | 18 mm |
| Diameter of holder 2 | 23 mm |
| Size | 56 |
| Nominal length | 54.5 mm |
| Mounting position | Any |
| Max. rotational speed | 5500 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 172 kgmm ² |
| Transferable torque | 60 Nm |
| Product weight | 466 g |
| Note on materials | RoHS-compliant |