

Manifold MHA3-PR2-3-1/8

Part number: 525221

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|------------------------------------|
| Max. no. of valve positions | 2 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Sub-base mounting type | With through-hole With DIN rail |
| Pneumatic valve mounting type | With internal thread |
| Pneumatic connection 1/33 | G1/4 |
| Pneumatic connection 2 | Internal thread G1/8 |
| Pneumatic connection 3/11 | G1/4 |
| Material of sub-base | Wrought aluminum alloy |