

# Manifold MHA3-PR8-3-1/8

Part number: 525224

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                            |
|----------------------------------|----------------------------------|
| Max. no. of valve positions      | 8                                |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress    |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                |
| Sub-base mounting type           | With through-hole<br>With H-rail |
| Pneumatic valve mounting type    | With internal thread             |
| Pneumatic connection 1/33        | G1/4                             |
| Pneumatic connection 2           | Internal thread G1/8             |
| Pneumatic connection 3/11        | G1/4                             |
| Material of sub-base             | Wrought aluminum alloy           |