

Manifold MHA4-PR10-3-1/4

Part number: 525238

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. no. of valve positions	10
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1710 g
Sub-base mounting type	With through-hole With H-rail
Pneumatic valve mounting type	With internal thread
Pneumatic connection 1/33	G3/8
Pneumatic connection 2	Internal thread G1/4
Pneumatic connection 3/11	G3/8
Material of sub-base	Wrought aluminum alloy