

Intermediate position attachment SLG-Z-8/12-A

Part number: 525680

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Structural design	Stop as rotary actuator system according to the rack-and-pinion principle
Position sensing	For proximity sensor
Operating pressure	1 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	33.5 g
Type of mounting	With through-hole and dowel pin
Pneumatic connection	M3
Stops material	Steel, nickel-plated
Seals material	PUR
Housing material	Hard-anodized