

Vacuum suction cup ESS-60-GT-G1/4

Part number: 525982

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Suction cup holder height compensator	6 mm
Min. workpiece radius	75 mm
Nominal width	2.5 mm
Suction cup diameter	60 mm
Suction cup volume	11.3 cm ³
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, deep
Operating pressure	-0.95 bar ... 0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 80 °C
Holding force at nominal operating pressure	134 N
Lateral force at nominal operating pressure	37 N
Product weight	21 g
Type of mounting	Via vacuum connection
Vacuum connection	G1/4
Color	Reddish brown
Shore hardness	72 +/- 5
Material of screwed plug	Wrought aluminum alloy
Note on materials	RoHS-compliant
Suction cup material	Vulkollan®