


Vacuum cup without connector ESV-80-GT

Part number: 526004

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Suction cup holder height compensator | 7.5 mm |
| Min. workpiece radius | 100 mm |
| Suction cup diameter | 80 mm |
| Suction cup volume | 28.6 cm ³ |
| Mounting position | Any |
| Structural design | Round, bell-shaped |
| Symbol | 00991485 |
| Suction cup shape | Round, deep |
| Operating pressure | -0.95 bar ... 0 bar |
| Nominal operating pressure | -0.7 bar |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | -10 °C ... 80 °C |
| Breakaway force at 70% vacuum | 245 N |
| Holding force at nominal operating pressure | 245 N |
| Lateral force at nominal operating pressure | 99 N |
| Product weight | 30.9 g |
| Type of mounting | Via vacuum connection |
| Color | Reddish brown |
| Shore hardness | 72 +/- 5 |
| Note on materials | RoHS-compliant |
| Suction cup material | Vulkollan® |