

Pressure gauge kit DPA-63-16-MA-SET

Part number: 526097

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|-----------------------------|-----------------------------|
| Symbol | 00991463 |
| Conforms to standard | EN 837-1 |
| Pressure gauge nominal size | 40 |
| Structural design | Bourdon tube pressure gauge |
| Type of mounting | With external thread |
| Operating pressure | 16 bar |
| Measurement accuracy class | 2.5 |
| Degree of protection | IP43 |
| Ambient temperature | 5 °C ... 60 °C |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Note on materials | RoHS compliant |
| Mounting position | Any |
| Pneumatic connection | G1/8 |
| Product weight | 250 g |