

# Pressure gauge kit DPA-100-16-MA-SET

Part number: 526099

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Symbol	00991463
Conforms to standard	EN 837-1
Pressure gauge nominal size	40
Structural design	Bourdon tube pressure gauge
Type of mounting	With external thread
Operating pressure	16 bar
Measurement accuracy class	2.5
Degree of protection	IP43
Ambient temperature	5 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Mounting position	Any
Pneumatic connection	G1/4
Product weight	305 g