

# Plug SD-SUB-D-ST25

Part number: 527522

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Type of mounting	With through-hole
Mounting position	Any
Product weight	51 g
Electrical connection	25-pin Plug Sub-D
DC operating voltage range	≤250 V
Operating voltage range AC	≤250 V
Current rating	5 A
Cable fitting	Pg11
Approved cable diameter	7 mm ... 12 mm
Degree of protection	IP65
Ambient temperature	-20 °C ... 80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA
Seals material	NBR
Material of pin contacts	Copper alloy Gold-plated