

Filter MS4N-LF-1/4-CRV

Part number: 531493

FESTO



 General operating condition

Data sheet

Feature	Value
Size	4
Series	MS
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	5 μm
Condensate drain	Manual, non-detenting
Structural design	Sinter filter with centrifugal separator
Bowl guard	Plastic bowl guard
Degree of condensate separation	$>75\%$
Symbol	00991520
Operating pressure	2 bar ... 12 bar
Normal nominal flow rate (normalized to DIN 1343)	1300 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4]
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Pore size	$<5\ \mu\text{m}$
Product weight	189 g
Type of mounting	With accessories
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Note on materials	RoHS compliant
Material of sub-base	Die-cast aluminum
Seals material	NBR
Compressed air filter material	Protective grounding
Housing material	Die-cast aluminum
Material of bowl	PC
Separating disc material	POM