

Quick coupling socket KD2-CK-3

Part number: 531621

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal width	2 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Normal nominal flow rate (normalized to DIN 1343)	68 l/min ... 88 l/min
Nominal flow rate standardized according to ISO 8778	73.7 l/min ... 95.4 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	11 g
Pneumatic connection 1	for pneumatic tubing outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut
Material of union nut	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Seals material	NBR
Material of spring	High-alloy stainless steel
Housing material	Brass, nickel-plated
Ball material	High-alloy stainless steel
Circlip material	High-alloy stainless steel
Valve body material	Brass
Material releasing sleeve	Brass, nickel-plated