

Quick coupling socket KD4-1/4-I

Part number: 531636

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal width	7.2 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Normal nominal flow rate (normalized to DIN 1343)	257 l/min ... 1292 l/min
Nominal flow rate standardized according to ISO 8778	278.6 l/min ... 1400.5 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	9.5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	88 g
Pneumatic connection 1	Internal thread G1/4
Note on materials	RoHS-compliant
Seals material	NBR
Material of spring	High-alloy stainless steel
Housing material	Brass, nickel-plated
Threaded coupling material	Brass, nickel-plated
Inner raceway material	Brass
Circlip material	High-alloy stainless steel
Material of pins	high-alloy stainless steel
Valve body material	Brass
Material releasing sleeve	PP