

Sealing ring OK-3/4

Part number: 531775

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Based on norm | ISO 16030 |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Manual tightening at RT | Yes |
| Nominal tightening torque | 35 Nm |
| Tolerance for nominal tightening torque | ±10% |
| Product weight | 1 g |
| Pneumatic connection | G3/4 |
| Note on materials | RoHS compliant |
| Stops material | PA-reinforced |
| Seals material | TPE-U(PU) |