

Branching module MS6N-FRM-3/8-Y-Z

Part number: 531976

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Structural design	Branching module
Symbol	00995602
Operating pressure	0 bar ... 12 bar
Standard nominal flow rate in main flow direction 1 -> 2	8350 l/min
Standard nominal flow rate outlet at top	4700 l/min
Standard nominal flow rate outlet down	4800 l/min
Operating voltage range AC	0 V ... 250 V
DC operating voltage range	0 V ... 125 V
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	778 g
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Pneumatic connection 3	1/2 NPT
Pneumatic connection 4	1/2 NPT
Note on materials	RoHS compliant
Housing material	Die-cast aluminum