

Fine filter combination LFMBA-3/4-D-MAXI-DA

Part number: 532871

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------|--|
| Size | Maxi |
| Series | D |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 0.01 µm |
| Filter efficiency | 99.9999 % |
| Condensate drain | Manually rotating |
| Structural design | Fiber filter |
| Max. condensate volume | 80 ml |
| Bowl guard | Metal bowl guard |
| Symbol | 00991529 |
| Operating pressure | 0.1 MPa ... 1.6 MPa |
| Operating pressure | 1 bar ... 16 bar |
| Operating pressure | 14.5 psi ... 232 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [1:7:2] Inert gas |
| Temperature of medium | 1.5 °C ... 60 °C |
| Residual oil content | 0.01 mg/m ³ |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 2362 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G3/4 |
| Pneumatic connection 2 | G3/4 |
| Note on materials | RoHS-compliant |
| Compressed air filter material | Borosilicate fiber |
| Housing material | Die-cast zinc |
| Material of bowl | PC |