

Push-in T-fitting QBT-3/8-1/4-U

Part number: 533317

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal width	4.496 mm
Type of seal on screwed plug	Coating
Mounting position	Any
Design	T-shape
Pack size	5
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	0 °C ... 60 °C
Product weight	42.412 g
Type of mounting	External hexagon 11/16
Pneumatic connection 1	external thread 3/8 NPT
Pneumatic connection 2	for pneumatic tubing outer diameter 1/4"
Ambient temperature Fahrenheit	32 °F ... 140 °F
Releasing ring color	Gray
Note on materials	RoHS compliant
Housing material	PBT
Material of threaded seal	PTFE
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	high-alloy stainless steel