

# Installation kit MKRP-3

Part number: 533634

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                         |
|----------------------------------|-------------------------------|
| Size                             | 3                             |
| Min. bending radius              | 75 mm                         |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B2-L                |
| Ambient temperature              | 0 °C ... 60 °C                |
| Product weight                   | 160 g                         |
| Adapter material                 | Steel                         |
| Lock nut material                | Brass<br>Nickel-plated        |
| Reduction material               | Brass<br>Nickel-plated        |
| Material of pneumatic tubing     | PA                            |
| Protective conduit material      | PA                            |
| Material of pneumatic fitting    | PA                            |