

Plug FBS-SUB-9-WS-PB-K

Part number: 533780

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	40 mm
Height	64 mm
Length	17 mm
Type of mounting	4-40 UNC-2B
Product weight	46 g
Fieldbus interface	Sub-D, 9-pin, plug
Electrical connection 1	9-pin Sub-D plug
Electrical connection 2	Screw terminal
Baud rate	12 Mbit/s
Approved cable diameter	8 mm
Approved cable diameter	8 mm
Connection cross section	1 mm ²
Degree of protection	IP20
Ambient temperature	0 °C ... 60 °C
Storage temperature	-25 °C ... 80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing material	Metalized plastic