

Pneumatic muffler UC-M5-50

Part number: 534217

FESTO



[PDF](#) [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Mounting position | Any |
| Pack size | 50 |
| Symbol | 00991473 |
| Operating pressure | 0 MPa ... 1 MPa |
| Operating pressure | 0 bar ... 10 bar |
| Flow rate with respect to atmosphere | 350 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Noise level | 60 dB(A) |
| Ambient temperature | -10 °C ... 70 °C |
| Product weight | 0.4 g |
| Pneumatic connection | M5 |
| Cushioning insert material | PE |
| Material of screwed plug | PE |
| Note on materials | RoHS-compliant |