

# Pneumatic muffler UC-M7-50

Part number: 534218

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Pack size	50
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	800 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	58 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	1.2 g
Pneumatic connection	M7
Cushioning insert material	Protective grounding
Material of screwed plug	Protective grounding
Note on materials	RoHS compliant