

# Ball valve VAPB-1/2-F-40-F03

Part number: 534304

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Structural design	2-way ball valve
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	Rp1/2
Switching position indication	Slot direction = flow direction
Flange hole pattern	F03
Inside diameter	15 mm
Nominal width DN	15
Valve function	2/2
Flow direction	Reversible
Nominal pressure of fitting PN	40
Breakaway torque at differential pressure, nominal pressure, fitting PN	5 Nm
Breakaway torque at 10 bar differential pressure	3.5 Nm
Based on norm	ISO 5211
Symbol	00991458
Medium	Compressed air as per ISO 8573-1:2010 [-:~:] Inert gas Water Neutral liquids
Temperature of medium	-20 °C ... 150 °C
Flow rate Kv	17 m <sup>3</sup> /h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Brass, nickel-plated
Material number of housing	2.0402 CW617N
Seat seal material	PTFE

<b>Feature</b>	<b>Value</b>
Seals material	HNBR PTFE
Ball material	Brass Hard-chrome-plated
Material number for ball	2.0401 CW614N
Shaft material	Brass
Material number for shaft	2.0401 CW614N
Product weight	400 g
Corrosion resistance class (CRC)	1 - Low corrosion stress