

Sub-base CDSV5.0-AS-1/8

Part number: 534434

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. no. of valve positions	1
Nominal operating voltage DC	24 V
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	-5 °C ... 50 °C
Noise level	75 dB(A)
Degree of protection	IP65 IP66 IP67 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	690 g
Electrical connection	Cable
Type of mounting	With through-hole With internal thread
Venting hole connection	M5
Pilot exhaust air port 82/84	M5
Pilot air port 12	M5
Pilot air port 14	M5
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8
Pneumatic connection 3	G1/8
Pneumatic connection 4	G1/8
Pneumatic connection 5	G1/8
Note on materials	RoHS-compliant