

Plug FBS-RJ45-8-GS

Part number: 534494

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	33 mm
Height	41 mm
Length	20 mm
Product weight	15 g
Ethernet cable specification	Type: CAT.5 Individual wire diameter: 0.89 - 0.99 mm AWG 24-26, fine wire
Protection against direct and indirect contact	PELV
Approved cable diameter	4 mm ... 5.4 mm
Degree of protection	IP65 IP67 As per IEC 60529
Ambient temperature	-5 °C ... 60 °C
Storage temperature	-20 °C ... 70 °C
Relative air humidity	0 - 90% Non-condensating
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA-reinforced
Material of screws	Steel
Seals material	NBR