

# One-way flow control valve GRLA-3/8-QB-5/16-U

Part number: 534665

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Valve function	Exhaust air flow control non-return function
Pneumatic connection 1	QB-5/16
Pneumatic connection 2	3/8 NPT
Actuation type	Manual
Adjusting element	Slotted screw
Type of mounting	Screw-in With external thread
Standard nominal flow rate in flow control direction	3572.03 l/min
Standard nominal flow rate in non-return direction	2752.119 l/min ... 3648.305 l/min
Ambient temperature	0 °C ... 60 °C
Mounting position	Any
Symbol	00991452
Operating pressure for entire temperature range	-0.951 bar ... 7.998 bar
Standard flow rate in flow control direction 6 -> 0 bar	5529.7 l/min
Standard flow rate in non-return direction at 6 -> 0 bar	5529.661 l/min ... 5745.763 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364 Zone III
Temperature of medium	0 °C ... 60 °C
Max. tightening torque	21.964 Nm
Product weight	69.741 g
Material of screwed plug	Brass Nickel-plated
Note on materials	RoHS compliant
Seals material	NBR
Hollow bolt material	Brass Nickel-plated
Releasing ring material	POM
Knurled head material	Brass Nickel-plated

Feature	Value
Material of adjusting screw	Brass Nickel-plated
Swivel joint material	PBT-reinforced