


Air reservoir CRVZS-20

Part number: 534845

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Volume | 20 l |
| Mounting position | Condensate drain downwards |
| Conforms to standard | AD 2000 |
| Symbol | 00991474 |
| Operating pressure | -0.095 MPa ... 1.6 MPa |
| Operating pressure | -0.95 bar ... 16 bar |
| Operating pressure | -13.78 psi ... 232 psi |
| Certification | German Technical Control Board (TÜV) |
| CE marking (see declaration of conformity) | as per EU pressure equipment directive |
| UKCA marking (see declaration of conformity) | according to UK regulations for pressure equipment |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] Nitrogen |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| For use in the food industry | See supplementary material information |
| Temperature of medium | -10 °C ... 100 °C |
| Ambient temperature | -10 °C ... 100 °C |
| Max. tightening torque for connecting thread | 130 Nm |
| Max. tightening torque for condensate drain | 27 Nm |
| Product weight | 10208 g |
| Type of mounting | With through-hole |
| Condensate drain connection | G3/8 |
| Pneumatic connection | G1 |
| Note on materials | RoHS-compliant |
| Air reservoir material | High-alloy stainless steel |