

# Sub-base-SET MS12-AQT

Part number: 537139

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Any
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Product weight	1300 g
Pneumatic connection 1	1 NPT
Pneumatic connection 2	1 NPT
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Seals material	NBR