

Electronics module VMPA2-MPM-EMM-4

Part number: 537986

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Max. no. of valve positions	2
Max. no. of solenoid coils	4
Nominal pick-up current per solenoid coil	100 mA up to 30 ms
Nominal current with current reduction	20 mA after 30 ms
Corrosion resistance class (CRC)	(installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	20 g
Housing material	POM
Note on materials	RoHS compliant