

Connecting cable NEBV-S1G25-K-10-N-LE25

Part number: 538227

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Type of mounting | 4-40 UNC-2B |
| Product weight | 1750 g |
| Electrical connection 1 | Sub-D socket, 25-pin |
| Electrical connection 2 | Open end, 25-wire |
| Nominal operating voltage DC | 24 V |
| Cable length | 10 m |
| Cable characteristic | Standard |
| Min. cable bending radius | 105 mm |
| Cable diameter | 10.5 mm |
| Cable design | 20 x 0.25 mm ² + 5 x 0.34 mm ² |
| Degree of protection | IP65 IP67 In mounted state |
| Ambient temperature with flexible cable installation | -5 °C ... 50 °C |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Material of cable sheath | PVC |
| Housing material | PBT |
| Material of union nut | PA |
| Seals material | TPE-O |