


Moment compensator FKC-32

Part number: 538961

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Radial deviation +/-	2.5 mm
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Short-term maximum permissible load in direction of force +/-	3000 N
Long-term maximum permissible load in direction of force +/-	1400 N
Product weight	122.3 g
Note on materials	RoHS compliant
Articulated joint material	PA-reinforced
Ball stud material	High-alloy steel
Plate material	Wrought aluminum alloy