

# Plug socket NTSD-GD-9-M12-5POL-RK

Part number: 538999

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Electrical connection	5-pin Straight plug/screw terminal
Current rating	3 A
Approved cable diameter	6 mm ... 8 mm
Connection cross section	0.75 mm <sup>2</sup>
Degree of protection	IP67
Ambient temperature	-40 °C ... 85 °C
Note on materials	RoHS-compliant
Housing material	PA
Housing colour	Black