

# Rotary distributor

## GF-1/4-1/8

Part number: 539291

FESTO



 General operating condition

## Data sheet

Feature	Value
Nominal width	8 mm
Mounting position	Any
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Standard flow rate 1-2.1 (6->0)	1730 l/min
Standard flow rate 1-2.X open (6->0)	4050 l/min
Max. rotational speed	3000 rpm
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water (liquid, ice-free)
Information on operating and pilot media	Use 5 µm filter when operating with water Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Max. tightening torque	2.8 Nm
Max. axial force	50 N
Max. radial force	150 N
Nominal tightening torque	1.65 Nm
Tolerance for nominal tightening torque	±20%
Product weight	370 g
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/8
Note on materials	RoHS compliant
Housing material	Brass, nickel-plated
Shaft material	High-alloy steel