

Filter regulator PCRP-64-N14-12-C-R1-M-T19

Part number: 5394666

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | 64 |
| Series | P |
| Actuator lock | Regulating screw with locknut |
| Mounting position | Vertical $\pm 5^\circ$ |
| Grade of filtration | 5 μm |
| Condensate drain | Manual, rotating |
| Structural design | Filter regulator without pressure gauge |
| Conforms to standard | NACE MR0175/ISO 15156 (housing and bowl) |
| Max. condensate volume | 30 ml |
| Controller function | With primary pressure compensation With secondary exhausting |
| Symbol | 00991586 |
| Pressure gauge | Set up for G1/4 |
| Operating pressure | 0.1 MPa ... 2 MPa |
| Operating pressure | 1 bar ... 20 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.2 bar |
| Max. standard flow rate | 2400 l/min |
| Normal nominal flow rate (normalized to DIN 1343) | 1920 l/min |
| Explosion prevention and protection | Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Storage temperature | -60 °C ... 80 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:4:4] |
| Temperature of medium | -60 °C ... 80 °C |
| Ambient temperature | -60 °C ... 80 °C |
| Product weight | 1965 g |
| Type of mounting | With mounting kit |
| Pressure gauge connection | G1/4 |
| Pneumatic connection 1 | NPT1/4-18 |
| Pneumatic connection 2 | NPT1/4-18 |

| Feature | Value |
|---------------------------------------|----------------------------|
| Drain screw material | high-alloy stainless steel |
| Drain screw material number | 1.4404/316L |
| Material of filter support | Cast stainless steel |
| Filter support material number | 1.4409/CF3M(316L) |
| Note on materials | RoHS compliant |
| Material of mounting bracket | high-alloy stainless steel |
| Seals material | CR NBR VMQ |
| Material of spring | high-alloy stainless steel |
| Compressed air filter material | high-alloy stainless steel |
| Compressed air filter material number | 1.4404/316L |
| Housing material | Cast stainless steel |
| Material number of housing | 1.4409/CF3M(316L) |
| Material of adjusting screw | high-alloy stainless steel |
| Material of bowl | Cast stainless steel |
| Bowl material number | 1.4409/CF3M (316L) |