

# Plug socket MSSD-C-M16

Part number: 539709

FESTO



 [General operating condition](#)

## Data sheet

| Feature                  | Value  |
|--------------------------|--|
| Contact durability       | 50   |
| Type of mounting         | On air solenoid valve with M3 central screw  |
| Mounting position        | Any  |
| Product weight           | 38 g   |
| Electrical connection    | 3-pin<br>Angled socket<br>Type A<br>As per DIN EN 175301-803<br>Rectangular design |
| Cable fitting            | M16  |
| Approved cable diameter  | 6 mm ... 8 mm  |
| Connection cross section | 1.5 mm <sup>2</sup>  |
| Degree of protection     | IP65<br>As per IEC 60529   |
| Ambient temperature      | -20 °C ... 115 °C  |
| LABS (PWIS) conformity   | VDMA24364-B2-L   |
| Note on materials        | RoHS compliant   |
| Housing material         | PA-reinforced  |
| Seals material           | HNBR   |