

# Plug socket MSSD-C-M16

Part number: 539709

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Contact durability	50
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	38 g
Electrical connection	3-pin Socket, angled Form A as per DIN EN 175301-803 Rectangular design
Cable fitting	M16
Approved cable diameter	6 mm ... 8 mm
Connection cross section	1.5 mm <sup>2</sup>
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C ... 115 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA-reinforced
Seals material	HNBR