

Plug socket MSSD-E-M12

Part number: 539711

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Contact durability	50
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	11 g
Electrical connection 1	Angled socket, rectangular design, 3-pin, form C
Electrical connection 2	Screw terminal
DC operating voltage range	0 V ... 300 V
Operating voltage range AC	0 V ... 250 V
Current rating at 40° C	6 A
Cable fitting	M12
Approved cable diameter	4 mm ... 6 mm
Connection cross section	0.75 mm ²
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C ... 115 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing material	PA-reinforced
Housing colour	Black
Seals material	HNBR