

Ball valve actuator unit VZPR-BPD-22-R2

Part number: 540517

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---------------------------------|
| Structural design | Quarter turn actuator |
| Actuation type | Electrical Pneumatic |
| Mounting position | Any |
| Type of mounting | With internal thread |
| Fitting connection | Rp2 |
| Switching position indication | Knob direction = flow direction |
| Nominal width DN | 50 |
| Operating pressure of actuator | 1 bar ... 8.4 bar |
| Nominal pressure of fitting PN | 25 |
| Symbol | 00991921 |
| Temperature of medium | -20 °C ... 150 °C |
| Ambient temperature | -20 °C ... 80 °C |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Product weight | 5400 g |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |