

# Ball valve actuator unit VZPR-BPD-22-R212

Part number: 540874

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Structural design	Quarter turn actuator
Actuation type	Electrical Pneumatic
Mounting position	Any
Type of mounting	With internal thread
Fitting connection	Rp2 1/2
Switching position indication	Knob direction = flow direction
Nominal width DN	63
Operating pressure of actuator	1 bar ... 8.4 bar
Nominal pressure of fitting PN	25
Symbol	00991921
Temperature of medium	-20 °C ... 150 °C
Ambient temperature	-20 °C ... 80 °C
LABS (PWIS) conformity	VDMA24364 zone III
Product weight	7300 g
Corrosion resistance class (CRC)	1 - Low corrosion stress