

Gripper jaw blank BUB-HGDT-40

Part number: 541103

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---------------------------------------|
| Size | 40 |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 5 °C ... 60 °C |
| Product weight per gripper jaw | 60 g |
| Type of mounting | Via through-hole and centering sleeve |
| Note on materials | RoHS compliant |
| Blank material | Wrought aluminum alloy |