

Heavy-duty tubing PAN-R-10X1,9-SI

Part number: 541677

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	44 mm
Inside diameter	6.2 mm
Min. bending radius	25 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa ... 3.5 MPa
Temperature-dependent operating pressure	-0.95 bar ... 35 bar
Temperature-dependent operating pressure	-13.775 psi ... 507.5 psi
Certification	TÜV
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.0498 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Silver
Shore hardness	D 62 +/-3
Note on materials	RoHS compliant
Material of pneumatic tubing	TPE-A