

Branching module MS12-FRM-G

Part number: 541681

FESTO



 General operating condition

Data sheet

Feature	Value
Mounting position	Any
Structural design	Branching module
Symbol	00991510
Operating pressure	0 bar ... 20 bar
Standard nominal flow rate in main flow direction 1 -> 2	25000 l/min ... 42000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [-:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	3000 g
Type of mounting	In-line installation With accessories
Pneumatic connection 1	Manifold module
Pneumatic connection 2	Manifold module
Pneumatic connection 3	G2
Pneumatic connection 4	G1
Material of sub-base	Die-cast aluminum
Material of mounting bracket	Die-cast aluminum
Seals material	NBR
Housing material	Die-cast aluminum
Module connector material	Die-cast aluminum