

AS-i module ASI-4DI3DO-M12X2-5POL-Z

Part number: 542125



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| CE marking (see declaration of conformity) | As per EU EMC directive as per EU explosion protection directive (ATEX) As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| KC characters | KC EMC |
| Certification | c UL us - Listed (OL) |
| Explosion prevention and protection | Zone 2 (ATEX) Zone 2 (UKEX) Zone 22 (ATEX) Zone 22 (UKEX) |
| ATEX category gas | II 3G |
| ATEX category for dust | II 3D |
| Explosion protection certification outside the EU | EPL Dc (GB) EPL Gc (GB) |
| Type of ignition protection for gas | Ex ec IIC T4 Gc X |
| Type of (ignition) protection for dust | Ex tc IIIC T115°C IP67 Dc X |
| Explosive ambient temperature | -5°C ≤ Ta ≤ +50°C |