

Multi-pin node VABE-S6-1LF-C-M1-C36M

Part number: 543412

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Based on norm	EN 61984
Mounting position	Any
Max. no. of valve positions	16 for double-solenoid valves 32 for single-solenoid valves
Max. residual current	6 A
Nominal operating voltage DC	24 V
Surge resistance	1.5 kV
Current rating at 40° C	1 A
Contamination level	3
Permissible voltage fluctuations	+/- 10%
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	545 g
Electrical actuation	Multi-pin
Electrical connection	Socket/terminal strip
Cover material	PA
Housing material	Die-cast aluminum