

Multi-pin node VABE-S6-1LT-C-M1-S37

Part number: 543414

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Max. no. of valve positions	16 for double-solenoid valves 32 for single-solenoid valves
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10%
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	459 g
Electrical actuation	Multi-pin
Electrical connection	Cable with plug
Cover material	PA
Housing material	Die-cast aluminum