

# Multi-pin node VABE-S6-1LF-C-M1-R19

Part number: 543415

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Max. no. of valve positions	16 for monostable pneumatic valves 8 for bistable pneumatic valves
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	539 g
Electrical actuation	Multi-pin
Electrical connection	19-pin Plug as per CNOMO E03.62.530.N
Cover material	PA
Housing material	Die-cast aluminum