



Regulator plate VABF-S3-1-R1C2-C-10

Part number: 543527

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Width	26 mm
Based on norm	ISO 15407-1
Mounting position	Any
Pneumatic vertical stacking	Pressure regulator for 1
Controller function	Constant output pressure With secondary exhausting
Symbol	00992227
Optional pressure gauge	Possible
Pressure regulation range MPa	0.05 MPa ... 0.85 MPa
Pressure regulation range	0.5 bar ... 8.5 bar
Pressure regulation range psi	7.25 psi ... 123.25 psi
Inlet pressure 1	0.5 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	305 g
Vertical stacking mounting type	On manifold sub-base On individual sub-base
Pressure gauge connection	With retaining clamp
Note on materials	RoHS compliant
Material of operator panel	PA
Controller housing material	Die-cast aluminum