

Vertical pressure supply plate VABF-S2-1-P1A3-G38

FESTO

Part number: 546093



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Width | 43 mm |
| Based on norm | ISO 5599-2 |
| Mounting position | Any |
| Pneumatic vertical stacking | Alternative pressure supply for 1 |
| Symbol | 00991883 |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Normal nominal flow rate (normalized to DIN 1343) | 1300 l/min |
| CE marking (see declaration of conformity) | as per EU simple pressure vessel directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP65 NEMA 4 |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 340 g |
| Vertical stacking mounting type | On manifold sub-base On individual sub-base |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast aluminum |