

Double nipple E-G3/4-3/4NPT

Part number: 546549

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	17.9 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	60 Nm
Max. tightening torque, pneumatic connection 2	32 Nm
Nominal tightening torque	45 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	164.88 g
Pneumatic connection 1	G3/4
Pneumatic connection 2	3/4 NPT
Note on materials	RoHS-compliant