

# Adapter AD-G3/4-3/4NPT-I

Part number: 546550

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	18.3 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	60 Nm
Max. tightening torque, pneumatic connection 2	32 Nm
Nominal tightening torque	45 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	195.64 g
Pneumatic connection 1	External thread G3/4
Pneumatic connection 2	Female thread 3/4 NPT
Note on materials	RoHS-compliant
Seals material	PVC
Housing material	Steel, galvanized